# Pro**Labs**

#### SFP-10GB-PDAC5MLZ-J-C

Juniper Networks<sup>®</sup> Compatible TAA 10GBase-CU SFP+ to SFP+ Direct Attach Cable (Passive Twinax, 5m, 28AWG, LSZH)

## Features:

- SFF-8431/8432 and INF-8074i Compliant
- Up to 10.3125Gbps
- IEEE802.3ba Standard
- 28AWG
- Passive copper
- Operating Temperature 0 to 70 Celsius
- RoHS 2.0 compliant and lead-free



Applications: • 10GBase-CU

## **Product Description**

This is a Juniper Networks<sup>®</sup> Compatible 10GBase-CU SFP+ to SFP+ LSZH direct attach cable that operates over passive copper with a maximum reach of 5m. It has been programmed, uniquely serialized, and data-traffic and application tested to ensure it is 100% compliant and functional. We stand behind the quality of our products and proudly offer a limited lifetime warranty. This cable is TAA (Trade Agreements Act) compliant and is built to comply with MSA (Multi-Source Agreement) standards.

ProLabs' transceivers are RoHS compliant and lead-free.

TAA refers to the Trade Agreements Act (19 U.S.C. & 2501-2581), which is intended to foster fair and open international trade. TAA requires that the U.S. Government may acquire only "U.S. – made or designated country end products."



Rev. 020723

# **Regulatory Compliance**

- ESD to the Electrical PINs: compatible with MIL-STD-883 Method 3015.
- ESD to the Duplex LC Receptacle: compatible with IEC 61000-4-2.
- Immunity: compatible with IEC 61000-4-3.
- EMI: compatible with FCC Part 15 Class B EN55022 Class B (CISPR 22B) VCCI Class B.
- Laser Eye Safety: compatible with FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1, 2.
- RoHS: compliant with 2002/95/EC 4.1&4.2 2005/747/EC.

#### **Absolute Maximum Ratings**

Parameter	Symbol	Min.	Тур.	Max.	Unit
Supply Voltage	Vcc	3.13	3.3	3.47	V
Storage Temperature	Tstg	-40		85	°C
Operating Case Temperature	Тс	0		70	°C
Humidity	RH	5		85	%
Data Rate			10		Gbps

#### **Physical Characteristics**

Parameter	Symbol	Min.	Тур.	Max.	Unit
Length	L			5	М
AWG				28	AWG
Jacket Material	LSZH, Black				

## **Electrical Characteristics**


Parameter	Symbol	Min.	Тур.	Max.	Unit
Resistance	Rcon			3	Ω
Insulation Resistance	Rins			10	ΜΩ
Raw Cable Impedance	Zca	95	100	110	Ω
Mated Connector Impedance	Zmated	85	100	110	Ω
Insertion Loss at 12.89GHz	SDD21			17.04	dB
Return Loss at 12.89GHz	SDD11/22	Return_Loss(f) $\geq$ $\begin{cases} 12 - 2\sqrt{f}, & 0.05 \leq f < 4.1 \\ 6.3 - 13\log 10\left(\frac{f}{5.5}\right), & 4.1 \leq f \leq 10 \end{cases}$			dB
Rise Time (20-80%)				34	ps

Pin	Logic	Symbol	Name/Description	Plug Note Sequence	
1		VeeT	Module Transmitter Ground.	1	3
2	LVTTL-O	Tx_Fault	1odule Transmitter Fault. 3		4
3	LVTTL-I	Tx_Disable	Transmitter Disable. Turns off transmitter laser output.	3	5
4	LVTTL-I/O	SDA	2-Wire Serial Interface Data. Same as MOD_DEF2 in INF-8074i.	3	
5	LVTTL-I/O	SCL	2-Wire Serial Interface Clock. Same as MOD_DEF1 in INF-8074i.	3	
6		MOD_ABS	Module Absent. Connected to VeeT or VeeR in the module.	3	
7	LVTTL-I	RSO	Rate Select 0. Optionally controls the SFP+ module receiver.	3	6
8	LVTTL-O	Rx_LOS	Receiver Loss of Signal indication. In FC, designated as Rx_LOS. In Ethernet, designated as Signal Detect.	3	4
9	LVTTL-I	RS1	Rate Select 1. Optionally controls SFP+ module transmitter.	3	6
10		VeeR	Module Receiver Ground.	1	3
11		VeeR	Module Receiver Ground.	1	3
12	CML-O	RD-	Receiver Inverted Data Output.	3	
13	CML-O	RD+	Receiver Non-Inverted Data Output.	3	
14		VeeR	Module Receiver Ground.	1	3
15		VccR	Module Receiver 3.3V Supply.	2	
16		VccT	Module Transmitter 3.3V Supply.	2	
17		VeeT	Module Transmitter Ground.	1	3
18	CML-I	TD+	Transmitter Non-Inverted Data Input.		
19	CML-I	TD-	Transmitter Inverted Data Input. 3		
20		VeeT	Module Transmitter Ground.	1	3


## Notes:

- 1. Labeling as inputs (I) and outputs (O) are from the perspective of the module.
- 2. The case makes electrical contact to the cage before any of the board edge contacts are made.
- 3. The module signal ground contacts, VeeR and VeeT, should be isolated from the module case.
- 4. This contact is an open collector/drain output contact and shall be pulled up on the host. Pull-ups can be connected to one of several power supplies; however, the host board design shall ensure that no module contact has a voltage exceeding module VccT/R+0.5V.
- 5. Tx\_Disable is an input contact with a  $4.7k\Omega$  to  $10k\Omega$  pull-up to the VccT inside the module.
- 6. If implementing SFF-8079, contacts 7 and 9 in SFF-8431 are used for AS0 and AS1, respectively.

#### **Electrical Pin-Out Details**



# **Mechanical Specifications**



Notes:

- 1. 2 pairs.
- 2. 100% conductor test conditions: 5V, insulation resistance of 10M $\Omega$ , and conduction resistance maximum of 3 $\Omega$ .

#### **About ProLabs**

Our experience comes as standard; for over 15 years ProLabs has delivered optical connectivity solutions that give our customers freedom and choice through our ability to provide seamless interoperability. At the heart of our company is the ability to provide state-of-the-art optical transport and connectivity solutions that are compatible with over 90 optical switching and transport platforms.

#### **Complete Portfolio of Network Solutions**

ProLabs is focused on innovations in optical transport and connectivity. The combination of our knowledge of optics and networking equipment enables ProLabs to be your single source for optical transport and connectivity solutions from 100Mb to 400G while providing innovative solutions that increase network efficiency. We provide the optical connectivity expertise that is compatible with and enhances your switching and transport equipment.

## **Trusted Partner**

Customer service is our number one value. ProLabs has invested in people, labs and manufacturing capacity to ensure that you get immediate answers to your questions and compatible product when needed. With Engineering and Manufacturing offices in the U.K. and U.S. augmented by field offices throughout the U.S., U.K. and Asia, ProLabs is able to be our customers best advocate 24 hours a day.

Contact Information ProLabs US Email: sales@prolabs.com Telephone: 952-852-0252

ProLabs UK

Email: salessupport@prolabs.com Telephone: +44 1285 719 600