
## E33209

## **Process adapter Tri-Clamp**





ADAPT IFM-CLAMP ISO2852 2" 3A



| Design                               |       | with leakage port   |
|--------------------------------------|-------|---|
| Pressure rating                      | [bar] | 16  |
| Tests / approvals                    |       |   |
| Pressure Equipment Directive         |       | A possible classification to PED depends on the application and has to be carried out by the user / operator. |
| Safety instructions                  |       | The compatibility between medium and product material has to be checked in all applications.                  |
| Mechanical data                      |       |   |
| Weight                               | [g]   | 226.5   |
| Materials (wetted parts)             |       | stainless steel (1.4435 / 316L) ; surface characteristics : Ra<0,4 / Rz 4                                     |
| Sensor connection                    |       | G 1 Aseptoflex Vario  |
| Process connection                   |       | Clamp DN50 (2") DIN 32676 (ISO 2852)  |
| Sealing                              |       | Gasket  |
| Hygienic equipment clas<br>DIN 11866 | ss to | H4  |
| Accessories                          |       |   |
| Items supplied                       |       | O-ring: 1 x 24 x 2, EPDM, FDA compliant, E30054   |
| Accessories (optional)               |       | O-ring: 1 x 24 x 2, FKM, FDA compliant, E30123  |
|                                      |       | sealing ring: 1, PEEK, FDA compliant, E30124  |
| Remarks                              |       |   |
| Pack quantity                        |       | 1 pcs.  |
|                                      |       |   |