

# PRODUCT DATASHEET FA11199\_TINA-O

## TINA-O

~35° x 15° oval beam optimized for Osram Golden Dragon+. Assembly with holder and installation tape.

### **SPECIFICATION:**

| Dimensions     | Ø 16.1 mm |
|----------------|-----------|
| Height         | 10.1 mm   |
| Fastening      | tape      |
| ROHS compliant | yes 🛈     |



### MATERIALS:


| Component              | Туре        | Material     | Colour | Finish |
|------------------------|-------------|--------------|--------|--------|
| TINA-O-PLUS-O          | Single lens | PMMA         | clear  |        |
| TINA-O-PLUS-H-TAPE-WHT | Holder      | PC           | white  |        |
| TINA-TAPE3             | Таре        | Acrylic foam | black  |        |

### **ORDERING INFORMATION:**

| Component      |             | Qty in box | MOQ | MPQ | Box weight (kg) |
|----------------|-------------|------------|-----|-----|-----------------|
| FA11199_TINA-O | Single lens | 2016       | 288 | 144 | 4.2             |
| » Box size:    |             |            |     |     |                 |



## PRODUCT DATASHEET FA11199\_TINA-O



See also our general installation guide: www.ledil.com/installation\_guide



### **OPTICAL RESULTS (MEASURED):**

#### OSRAM Opto Semiconductors

LEDGeFWHM / FWTM14Efficiency90Peak intensity6.3LEDs/each optic1Light colourWRequired components:

Golden Dragon+ 14.0 + 34.0° / 32.0 + 60.0° 90 % 6.5 cd/lm 1 White



## **OPTICAL RESULTS (SIMULATED):**

| CREECIED<br>LED<br>FWHM / FWTM<br>Efficiency<br>Peak intensity<br>LEDs/each optic<br>Light colour<br>Required components:                     | XP-L HI<br>43.0 + 18.0° / 68.0 + 39.0°<br>88 %<br>2.7 cd/lm<br>1<br>White                     | 200<br>200<br>200<br>200<br>200<br>200<br>200<br>200   |
|---|---|--|
| OSRAM<br>Opto Semiconductors<br>LED<br>FWHM / FWTM<br>Efficiency<br>Peak intensity<br>LEDs/each optic<br>Light colour<br>Required components: | OSCONIQ P 3737 (2W version)<br>43.0 + 18.0° / 71.0 + 39.0°<br>86 %<br>2.6 cd/lm<br>1<br>White | 30, 12, 0, 72,<br>20, 20, 20,<br>22, 30,0<br>60, 60,<br>30, 90,<br>30, 90, |



## PRODUCT DATASHEET FA11199\_TINA-O

### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc. 228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd. # 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

### Local sales and technical support www.ledil.com/ where\_to\_buy

Shipping locations Salo, Finland Hong Kong, China

Distribution Partners www.ledil.com/ where\_to\_buy