


| | SW REFERENCE NO.: 628 ASSEMBLY | | | | | | |
|--------------------------------------|---|-----------------|-----------|--------------------|---|----|-------|
| 628 SERIES D-SUB (| DRAWN: C.B DATE: AUG. 01/2018 CHECKED: DATE: SCALE: 1:1 SHEET 1 DRAWING NUMBER: 628-037-620-262 ISSUE | DRAWN: C.B | | DATE: AUG. 01/2018 | | | |
| | | CHECKED: | | DATE: | | | |
| EDAC INC | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INCAND | SCALE: 1:1 | | SHEET | 1 | OF | 1 |
| TORONTO, ONTARIO CANADA | SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE | DRAWING NUMBER: | 628-037-0 | 620-262 | | | ISSUE |
| YOUR CONNECTION TO QUALITY & SERVICE | MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | PART NUMBER: | 628-037-6 | 620-262 | | | 1 |

WITHSTANDING VOLTAGE: 1000V AC rms







THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

