



# HellermannTyton®

NOTE:  
\* 1. INSIDE DIAMETERS ARE MEASURED IN THREE PLACES SPACED 120° APART EXCLUDING .015 WIDE RIB

\* CLAMP RANGE

POSITION	EFFECTIVE TOOTH ENGAGEMENT	DIAMETER
MINIMUM	25	3.841
NOMINAL	14	4.075
MAXIMUM	2	4.331

CHANGE IN DIA./TOOTH = .0213

DESIGN TEAM	INSTRUMENTS/DATE
ALL PROPERTIES RIGHTS IN THE SUBJECT MATTER ARE RESERVED EXCEPT WHERE SHOWN OTHERWISE BY THE EXCLUSIVE PROPERTY OF TYTON CORPORATION	
DATE	RELEASED BY

MATERIAL	VERIFIED DATE	UNITS	TOLERANCES	NAME	DATE	PART NAME	SCALE	CUSTOMER DRAWING NUMBER
13% GLASS FILLED NYLON 6/6 HEAT STABILIZED	3/10/93	mm	UNLESS OTHERWISE SPECIFIED X= .XX Y= .YY Z= .ZZ <=	K.A.C.	3/10/93	SNP-100	FULL	CP/CST\2100001A

SNP-100	CP2100-001-A
CATALOG NUMBER	PART NUMBER-REV