




## FCR24-10-6-A

Ruland FCR24-10-6-A, 5/8" x 3/8" Six Beam Coupling, Aluminum, Clamp Style, 1.500" OD, 2.250" Length





## **Description**

Ruland FCR24-10-6-A is a clamp style six beam coupling with 0.6250" x 0.3750" bores, 1.500" OD, and 2.250" length. It is machined from a single piece of material and features two sets of three spiral cuts. This gives it higher torque capacity, lower windup, and larger body sizes than single or four beam couplings and allows for use in light duty power transmission applications such as coupling a servo motor to a lead screw. FCR24-10-6-A is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. Ruland supplies this spiral coupling with Nypatch® anti-vibration hardware that allows for even seating of the screw, repeated screw installations, prevents galling, and maintains high holding power. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. FCR24-10-6-A is made from 7075 aluminum for lightweight and low inertia. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. FCR24-10-6-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

			-	•			
ப	ra	AII.	IC+	SINO	CITI	へつきょん	ne
	ıvı	uч	JUL	Suc		catio	JI IS

Product Specifications						
Bore (B1)	0.6250 in	Small Bore (B2)	0.3750 in			
B1 Max Shaft Penetration	1.075 in	B2 Max Shaft Penetration	1.075 in			
Outer Diameter (OD)	1.500 in	Bore Tolerance	+0.001 in / -0.000 in			
Length (L)	2.250 in	Clearance Diameter (C) MAX	1.642 in			
Recommended Shaft Tolerance	+0.0000 in / -0.0005 in	Cap Screw	M5			
Screw Material	Alloy Steel with Nypatch®	Hex Wrench Size	4.0 mm			
Screw Finish	Black Oxide	Seating Torque	9.5 Nm			
Number of Screws	2 ea	Dynamic Torque Reversing	23.75 lb-in			
Angular Misalignment	3°	<b>Dynamic Torque Non-Reversing</b>	47.5 lb-in			
Parallel Misalignment	0.030 in	Static Torque	95 lb-in			
Axial Motion	0.015 in	Torsional Stiffness	0.043 Deg/lb-in			
Moment of Inertia	0.1023 lb-in <sup>2</sup>	Maximum Speed	6,000 RPM			
Full Bearing Support Required?	Yes	Nypatch® Anti-Vibration Hardware?	Yes			
Zero-Backlash?	Yes	Balanced Design	Yes			
Torque Wrench	TW:BT-4C-3/8-86	Recommended Hex Key	Metric Hex Keys			
Material Specification	7075-T651 Extruded and Drawn Aluminum Bar	Temperature	-40°F to 225°F (-40°C to 107°C)			
Finish Specification	Bright, No Plating	Manufacturer	Ruland Manufacturing			
Country of Origin	USA	Weight (lbs)	0.295000			
UPC	634529008539	Tariff Code	8483.60.8000			
UNSPC	31163003					
Note 1	Torque ratings are at maximum misalignment.					
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.					
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the machined beams. Please consult technical support for more assistance.					
Prop 65	65 ▲ WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="https://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> .					

## **Installation Instructions**

- 1. Align the bores of the FCR24-10-6-A six beam coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 3°, *Parallel Misalignment*: 0.030 in, *Axial Motion*: 0.015 in)
- 2. Fully tighten the M5 screw on one hub to the recommended seating torque of 9.5 Nm using a 4.0 mm hex torque wrench.
- 3. Before tightening the screws on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screws on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 1.075 in.