

Strain Gage Adhesive

OTHER ACCESSORIES USED IN AN M-BOND 200 INSTALLATION:

- CSM Degreaser or GC-6 Isopropyl Alcohol
- Silicon Carbide Paper
- M-Prep Conditioner A
- M-Prep Neutralizer 5A
- GSP-1 Gauze Sponges
- CSP-1 Cotton Applicators
- PCT-2M Gage Installation Tape



RoHS
COMPLIANT

DESCRIPTION

For routine experimental stress analysis applications under temperate environmental conditions, M-Bond 200 adhesive is ordinarily the best choice. This adhesive is very easy to handle, and cures almost instantly to produce an essentially creep-free, fatigue-resistant bond, with elongation capability of five percent or more.

M-Bond 200 is a cyanoacrylate that has been pretested and certified for use in bonding strain gages. It is an excellent general-purpose adhesive for laboratory and short-term field applications. The procedure for making a strain gage installation with M-Bond 200 is illustrated and described in detail in Instruction Bulletin B-127 included in each kit of adhesive.

The user should note that the performance of the adhesive can be degraded by the effects of time, humidity conditions, elevated temperature, and moisture absorption. Because of the latter effect, strain gage installations should always be covered with a suitable protective coating. When necessitated by more rigorous test requirements and/or environmental conditions, consideration should be given to one of the M-Bond epoxy adhesives, using the "Recommended Adhesives/Strain Gage Series" chart.

CHARACTERISTICS	
PARAMETER	DETAILS
CURE REQUIREMENTS*	One-minute thumb pressure, followed by a minimum two-minute delay before tape removal. Bond strength increases rapidly during first five minutes. Cure time must be extended under conditions of low temperature [$<70^{\circ}\text{F}$ ($<21^{\circ}\text{C}$)] or low humidity ($<40\%$ RH).
OPERATING TEMPERATURE RANGE	<p>Short Term: -300° to $+200^{\circ}\text{F}$ (-185° to $+95^{\circ}\text{C}$).</p> <p>Long Term: -25° to $+150^{\circ}\text{F}$ (-32° to $+65^{\circ}\text{C}$).</p>
ELONGATION CAPABILITIES	$>5\%$ at $+75^{\circ}\text{F}$ ($+24^{\circ}\text{C}$), 3% at $+75^{\circ}\text{F}$ ($+24^{\circ}\text{C}$) when used with CEA or EA/Option E strain gages.
SHELF LIFE	<p>Minimum 12 months when stored unopened at $+40^{\circ}\text{F}$ ($+5^{\circ}\text{C}$) or minimum 9 months when stored unopened at $+75^{\circ}\text{F}$ ($+24^{\circ}\text{C}$).</p> <p><i>Note:</i> To ensure a proper seal, wipe bottle spout clean and dry before replacing cap.</p> <p><i>Note:</i> Condensation rapidly degrades adhesive performance and shelf life; if refrigerated, allow adhesive to reach room-temperature before opening. Refrigeration after opening is not recommended.</p>
POT LIFE	Maximum 3 months at $+75^{\circ}\text{F}$ ($+24^{\circ}\text{C}$) (not to exceed date of expiration) after opening. Replace the cap immediately after each use.

PACKAGING OPTIONS	
KIT	BULK
<p>1 bottle (1 oz/28 g) Adhesive 1 brush-cap bottle (30 ml) Catalyst</p>	<p>1 bottle (1 oz/28 g) Adhesive 5 tubes (2 g each) Adhesive 16 bottles (1 oz/28 g each) Adhesive 12 brush-cap bottles (30 ml each) Catalyst</p>

*Reference: Instruction Bulletin B-127 for complete details.



Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.