

160-9402-900-C

Ciena® 160-9402-900 Compatible TAA 100GBase/OTU4-LR4 QSFP28 Transceiver Dual-Rate (SMF, 1295nm to 1309nm, 10km, LC, DOM)

Features:

- SFF-8665 Compliance
- Duplex LC Connector
- Single-mode Fiber
- Commercial Temperature 0 to 70 Celsius
- Hot Pluggable
- Metal with Lower EMI
- Excellent ESD Protection
- RoHS Compliant and Lead Free



Applications:

- 100GBase Ethernet
- OTN OTU4
- Access and Enterprise

Product Description

This Ciena® 160-9402-900 compatible QSFP28 transceiver provides 100GBase/OTU4-LR4 throughput up to 10km over single-mode fiber (SMF) using a wavelength of 1295nm to 1309nm via an LC connector. It is guaranteed to be 100% compatible with the equivalent Ciena® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. This transceiver is Trade Agreements Act (TAA) compliant. We stand behind the quality of our products and proudly offer a limited lifetime warranty.

ProLabs' transceivers are RoHS compliant and lead-free.

TAA refers to the Trade Agreements Act (19 U.S.C. & 2501-2581), which is intended to foster fair and open international trade. TAA requires that the U.S. Government may acquire only "U.S. – made or designated country end products."



Regulatory Compliance

- ESD to the Electrical PINs: compatible with MIL-STD-883E Method 3015.4
- ESD to the LC Receptacle: compatible with IEC 61000-4-3
- EMI/EMC compatible with FCC Part 15 Subpart B Rules, EN55022:2010
- Laser Eye Safety compatible with FDA 21CFR, EN60950-1& EN (IEC) 60825-1,2
- RoHS compliant with EU RoHS 2.0 directive 2015/863/EU

Absolute Maximum Ratings

| Parameter | Symbol | Min. | Тур. | Max. | Unit |
|----------------------------|--------|------|-------------|------|------|
| Power Supply Voltage | VCC | -0.5 | | 4.0 | V |
| Storage Temperature | Ts | -40 | | 85 | °C |
| Operating Case Temperature | Тс | -5 | 25 | 70 | °C |
| Relative Humidity | RH | 5 | | 95 | % |
| Data Rate PER Channel | | | 25.78/28.05 | | Gb/s |

Electrical Characteristics

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Notes | |
|--|-----------|-------|------|-------|-------|-------|--|
| Supply Voltage | VCC | 3.135 | 3.3 | 3.465 | V | | |
| Module Supply Current | Icc | | | 1100 | mA | | |
| Power Dissipation | PD | | | 3500 | mW | | |
| Transmitter | | | | | | | |
| Single-ended Input Voltage Tolerance | | -0.3 | | 4.0 | V | | |
| Input Differential Impedance | ZIN | | 100 | | Ω | | |
| Differential Data Input Swing | VIN, P-P | 190 | | 700 | mVP-P | | |
| AC Common Mode Input Voltage Tolerance | | 15 | | | mV | | |
| Differential Input Voltage Swing Threshold | | 50 | | | mVpp | | |
| Receiver | | | | | | | |
| Single-ended Output Voltage | | -0.3 | | 4.0 | V | | |
| Output Differential Impedance | ZO | 90 | 100 | 110 | Ω | | |
| Differential Data Output Swing | VOUT, P-P | 300 | | 850 | mVP-P | | |
| AC Common Mode Output Voltage | | | | 7.5 | mV | | |

Optical Characteristics

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Notes | |
|--|---------|---------|---------|---------|------|-------|--|
| Transmitter | | | | | | | |
| Launch Optical Power per Lane | Ро | -4.3 | | +4.5 | dBm | 1 | |
| Total Launch Optical Power | Po | | | +10.5 | dBm | 1 | |
| | L1 | 1294.53 | 1295.56 | 1296.59 | nm | | |
| | L2 | 1299.02 | 1300.05 | 1301.09 | nm | | |
| Center Wavelength Range | L3 | 1303.54 | 1304.58 | 1305.63 | nm | | |
| | L4 | 1308.09 | 1309.14 | 1310.19 | nm | | |
| Extinction Ratio | EX | 4.0 | | | dB | 2 | |
| Spectral Width (-20dB) | Δλ | | | 1 | nm | | |
| Side Mode Suppression Ratio | SMSR | 30 | | | dB | | |
| Optical Return Loss Tolerance | ORLT | | | 20 | dB | | |
| Pout @TX-Disable Asserted | Poff | | | -30 | dBm | 1 | |
| Eye Mask Coordinates {X1, X2, X3, Y1, Y2, Y3} {0.25, 0.4, 0.45, 0.25, 0.28, 0.4} | | | | | | | |
| Receiver | | | | | | | |
| | L1 | 1294.53 | 1295.56 | 1296.59 | nm | | |
| | L2 | 1299.02 | 1300.05 | 1301.09 | nm | | |
| Center Wavelength Range | L3 | 1303.54 | 1304.58 | 1305.63 | nm | | |
| | L4 | 1308.09 | 1309.14 | 1310.19 | nm | | |
| Sensitivity per Channel (OMA) | S | | | -8.6 | dBm | 2 | |
| Overload (each channel) | POL | 4.5 | | | dBm | 2 | |
| Damage Threshold (each channel) | Pdamage | 5.5 | | | dBm | | |
| Optical Return Loss | ORL | 26 | | | dB | | |
| LOS De-Assert | LOSD | | | -11.6 | dBm | | |
| LOS Assert | LOSA | -24 | | | dBm | | |
| LOS Hysteresis | | 0.5 | | | dB | | |

Notes:

- 1. The optical power is launched into SMF.
- 2. Measured with a PRBS 2^{31} -1 test pattern @28.05Gbps.


Pin Descriptions

| Pin | Logic | Symbol | Name/Descriptions | Ref. |
|-----|------------|---------|---|------|
| 1 | | GND | Module Ground | 1 |
| 2 | CML-I | Tx2- | Transmitter inverted data input | |
| 3 | CML-I | Tx2+ | Transmitter non-inverted data input | |
| 4 | | GND | Module Ground | 1 |
| 5 | CML-I | Tx4- | Transmitter inverted data input | |
| 6 | CML-I | Tx4+ | Transmitter non-inverted data input | |
| 7 | | GND | Module Ground | 1 |
| 8 | LVTTL-I | MODSEIL | Module Select | 2 |
| 9 | LVTTL-I | ResetL | Module Reset | 2 |
| 10 | | VCCRx | +3.3v Receiver Power Supply | |
| 11 | LVCMOS-I | SCL | 2-wire Serial interface clock | 2 |
| 12 | LVCMOS-I/O | SDA | 2-wire Serial interface data | 2 |
| 13 | | GND | Module Ground | 1 |
| 14 | CML-O | RX3+ | Receiver non-inverted data output | |
| 15 | CML-O | RX3- | Receiver inverted data output | |
| 16 | | GND | Module Ground | 1 |
| 17 | CML-O | RX1+ | Receiver non-inverted data output | |
| 18 | CML-O | RX1- | Receiver inverted data output | |
| 19 | | GND | Module Ground | 1 |
| 20 | | GND | Module Ground | 1 |
| 21 | CML-O | RX2- | Receiver inverted data output | |
| 22 | CML-O | RX2+ | Receiver non-inverted data output | |
| 23 | | GND | Module Ground | 1 |
| 24 | CML-O | RX4- | Receiver inverted data output | |
| 25 | CML-O | RX4+ | Receiver non-inverted data output | |
| 26 | | GND | Module Ground | 1 |
| 27 | LVTTL-O | ModPrsL | Module Present, internal pulled down to GND | |
| 28 | LVTTL-O | IntL | Interrupt output, should be pulled up on host board | 2 |
| 29 | | VCCTx | +3.3v Transmitter Power Supply | |
| 30 | | VCC1 | +3.3v Power Supply | |
| 31 | LVTTL-I | LPMode | Low Power Mode | 2 |
| 32 | | GND | Module Ground | 1 |
| 33 | CML-I | Tx3+ | Transmitter non-inverted data input | |
| 34 | CML-I | Tx3- | Transmitter inverted data input | |
| 35 | | GND | Module Ground | 1 |
| 36 | CML-I | Tx1+ | Transmitter non-inverted data input | |
| 37 | CML-I | Tx1- | Transmitter inverted data input | |
| 38 | | GND | Module Ground | 1 |


Notes:

- 1. Module circuit ground is isolated from module chassis ground with in the module.
- 2. Open collector; should be pulled up with 4.7k-10k ohms on host board to a voltage between 3.15V and 3.6V.


Electrical Pin-out Details




Recommended Host Board Power Supply Filter Network





Recommended Application Interface Block Diagram



Mechanical Specifications







About ProLabs

Our experience comes as standard; for over 15 years ProLabs has delivered optical connectivity solutions that give our customers freedom and choice through our ability to provide seamless interoperability. At the heart of our company is the ability to provide state-of-the-art optical transport and connectivity solutions that are compatible with over 90 optical switching and transport platforms.

Complete Portfolio of Network Solutions

ProLabs is focused on innovations in optical transport and connectivity. The combination of our knowledge of optics and networking equipment enables ProLabs to be your single source for optical transport and connectivity solutions from 100Mb to 400G while providing innovative solutions that increase network efficiency. We provide the optical connectivity expertise that is compatible with and enhances your switching and transport equipment.

Trusted Partner

Customer service is our number one value. ProLabs has invested in people, labs and manufacturing capacity to ensure that you get immediate answers to your questions and compatible product when needed. With Engineering and Manufacturing offices in the U.K. and U.S. augmented by field offices throughout the U.S., U.K. and Asia, ProLabs is able to be our customers best advocate 24 hours a day.

Contact Information

ProLabs US

Email: sales@prolabs.com Telephone: 952-852-0252

ProLabs UK

Email: salessupport@prolabs.com Telephone: +44 1285 719 600